



## Genlab Moisture Extraction Ovens



Model Shown - ME/500/TDIG



Model Shown - ME/100/TDIG

The Genlab range of Moisture Extraction Ovens are specifically designed to provide rapid drying and removal of excess moisture. Increased air circulation around the chamber and larger extraction vents offers superior drying times.

It features our latest touch screen control system which offers intuitive control and excellent accuracies designed for stable drying conditions.

### Features

- 14 sizes 50 to 1000 litres
- High speed air circulation
- Increased ventilation
- Temp range 40°C to 250 °C  
(50°C to 250 °C above 250L models)
- On screen historical trending (48hours)
- 8 Stage profile control
- Count down timer
- 24/7 real time clock operation
- Manual or automatic overheat reset
- High accuracy Pt100B duplex sensors <0.8 °C
- Excellent stability <0.8 °C
- Low chamber uniformity

### Options

- Stainless steel chamber
- Audible warnings
- Explosion relief panels
- Drip trays
- Access ports (25, 50, 75 or 100mm)
- Traceable calibration to national standards
- Bespoke stands and stacking kits
- Extended warranty
- Bespoke solutions available upon request
- Castor wheels (only available on 250/350 models  
- fitted as standard on 425/500/650/750/850 and 1000 models)

## Design

The ovens are specifically designed for the rapid extraction of moisture and are fitted with larger 75mm diameter outlet vents, suitable for connection to most external extraction systems.

The exterior is constructed from sheet steel and finished in an easy clean powder coated paint. The interior chamber is made from mild steel coated with aluminium (CLAD), with a stainless steel chamber available as an option. It is also fitted with fixed shelf runners and removable chrome plated wire grid shelves.

## Heating

Heated by Incoloy sheathed elements positioned in the side fan duct for all units.

## Controls

The control system comprises of a bespoke touch screen user interface that offers both accurate temperature control and an integral overheat system by using 2 individual PT100 sensors. Advanced features can be turned on and off to suit bespoke heating applications and tailored to customer preference. Oven trending is displayed for up to 48 hours and optional upgrades are available for alarm outputs.



## Sizes and Specifications

GenlabReference Number	Capacity (litres)	Internal Dims. (H x W x D cms)	External Dims. (H x W x D cms)	Shelves/Positions	Wattage	Voltage	Weight (kg)
ME/50/TDIG	50	45 x 32 x 35	58 x 68 x 50	2..3	750	230	35
ME/75/TDIG	75	45 x 49 x 35	58 x 85 x 50	2..3	1000	230	45
ME/100/TDIG	100	45 x 49 x 46	58 x 85 x 61	3..4	1000	230	55
ME/125/TDIG	125	55 x 49 x 46	66 x 85 x 61	3..5	1500	230	65
ME/150/TDIG	145	55 x 49 x 54	66 x 85 x 69	3..5	1500	230	70
ME/200/TDIG	200	75 x 49 x 54	86 x 85 x 69	4..7	2000	230	85
ME/250/TDIG	240	91 x 51 x 52	117 x 98 x 69	5..7	2000	230	90
ME/350/TDIG	345	91 x 61 x 62	117 x 108 x 79	5..7	2500	230	120
ME/425/TDIG	425	91 x 61 x 77	117 x 110 x 95	5..7	3000	230	150
ME/500/TDIG	535	114 x 61 x 77	140 x 110 x 95	5..9	3000	230	165
ME/650/TDIG	675	114 x 77 x 77	140 x 142 x 95	5..9	6000	415	280
ME/750/TDIG	760	128 x 77 x 77	164 x 142 x 95	5..10	6000	415	300
ME/850/TDIG	840	142 x 77 x 77	178 x 142 x 95	5..11	6000	415	320
ME/1000/TDIG	1005	142 x 77 x 92	178 x 142 x 110	5..11	6000	415	340

## Ordering

All units have CLAD interior with touch screen interface, high speed air circulation and increased vent size as standard. Where options are required, simply add the option code to the original reference.

E.g. ME/1000/TDIG with CAL cert and drip tray becomes ME/1000/TDIG/SPC/DT.

Contact sales for bespoke options.

## Option Codes

Stainless Steel Chamber - SS

Drip Trays - DT

Stands/Stacking Kits - STAND

Audible Warning - AWA


Access Ports -AP

Extended Warranty - X1

Explosion Relief Panels - EXP

Traceable Calibration - SPC

Castor Wheels (250-350L units only) - 1108



Tanhouse Lane, Widnes, Cheshire WA8 0SR  
Tel 0151 424 5001 enquiries@genlab.co.uk www.genlab.co.uk

